

YGA6CTC10 Compression Grounding Lug, #6 Sol/Str, #10 Stud



By Burndy
Catalog # YGA6CTC10

Grounding Irreversible Compression Terminals 6 sol 6 str #10 bolt size

General

Catalog Number	YGA6CTC10
Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Material	Copper
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810146026
UPC 12 Digit	7818101460266

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.89 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.42 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	#10

Conductor Related

Conductor - Copper Solid Size	6
Conductor - Copper Solid Size Range	6
Conductor - Copper Str Size	6 Sol./6 Str.
Conductor - Copper Str Size Range	6 Sol./6 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 467 • Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SD209500](#)