

YGA8CTC14 Compression Grounding Lug, #8 AWG Cu, 1-Hole, 1/4" Stud



By Burndy
Catalog # [YGA8CTC14](#)

HYLUG™ Copper Compression Terminal for Grounding; 1-Hole; 1/4" Stud; Long Barrel; Accommodates: #8 AWG

General

Catalog Number	YGA8CTC14
Color Code	Red
Connector Type	Terminal
Die Index	49
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
Type	Terminals
UPC	781810102442
UPC 12 Digit	7818101024422

Dimensions

Dimension - B Length fraction	4/5 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size inch	0.25 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper Solid Size	8
Conductor - Copper Solid Size Range	8
Conductor - Copper Str Size	8 Sol./8 Str.
Conductor - Copper Str Size Range	8 Sol./8 Str.
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YGA6CTC14_LineArt](#)
- [Sales Drawings - SD209500](#)
- [Specifications - YGA8CTC14](#)