

YGHC26C2 Compression Grounding C-TAP Connector, 1-2/0 AWG Str, 3/8" Rod Run, #6 AWG Sol-#2 AWG Str Tap

By Burndy
Catalog # [YGHC26C2](#)



Copper Compression C Connector, 1 - 2/0 AWG(Str), 3/8" Rod (Run) & 6 AWG(Sol)- 2 AWG(Str) (Tap).

Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial Cables

General

Catalog Number	YGHC26C2
Connector Type	Tap
Die Index	O
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of	1
Crimps Required	
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810221020
UPC 12 Digit	7818102210200

Dimensions

Dimension - B Length inch	0.75 in
Dimension - Height fraction	1-25/61 in
Dimension - Height inch	1.41 in
Dimension - Height mm	35.8 mm
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap Range	6 AWG-2 AWG
Conductor - Copper Str Run	1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	1 AWG-2/0 AWG
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Rod Run	3/8 in
Conductor - Rod Run Range	3/8 in

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	14800

Product Assets

- [3D Models - YGHC26C2_MODEL-PDF](#)
- [3D Models - YGHC26C2_MODEL-STEP](#)
- [3D Models - YGHC26C2_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog

Product Cross Section Image(s) - BUR_YGHC_LineArt
Sales Drawings - SD086223-01
Specifications - YGHC26C2



©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YGHC26C2-SPEC-EN | REV 10/2024