

# YGHC29C26 Compression Grounding C-TAP Connector

By Burndy  
Catalog # [YGHC29C26](#)



Copper Compression C Connector, 3/0 AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 6 AWG(Sol) - 2/0 AWG(Str) (Tap).

## Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

## Application

For Direct Burial Cables

## General

Catalog Number	YGHC29C26
Connector Type	Tap
Die Index	997
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of	1
Crimps Required	
Plated	N
Plating Type	Unplated
Sub Brand	HYGROUND, HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810221044
UPC 12 Digit	7818102210444

## Dimensions

Dimension - B Length fraction	0.75 in
Dimension - B Length inch	0.75 in
Dimension - Height fraction	1-32/33 in
Dimension - Height inch	1.97 in
Dimension - Height mm	50 mm
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

## Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
------------------------------	-------------------------------------------------------------

Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Str Run	3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	3/0 AWG-250 kcmil
Conductor - Copper Str Tap	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	7 AWG-2/0 AWG
Conductor - Rod Run	1/2 in;5/8 in
Conductor - Rod Run Range	1/2 in-5/8 in

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• IEEE 837</li> <li>• UL468A-468B</li> </ul>
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	50
Pallet Quantity	9250

## Product Assets

- [360 Product View](#)
- [3D Models - YGHC29C26\\_MODEL-STEP](#)
- [3D Models - YGHC29C26\\_MODEL-IGES](#)
- [3D Models - YGHC29C26\\_MODEL-PDF](#)
- [3D Product View](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)



A Hubbell brand