

# YGHS26 Compression Grounding Splice, 2/0 AWG Cu

By Burndy  
Catalog # YGHS26



HYGROUND® Grounding Irreversible Compression Splice; Heavy Duty; Accommodates: 2/0 AWG; 1.89" Length

## Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

## Application

For Direct Burial In Earth Or Concrete

## General

Catalog Number	YGHS26
Connector Type	Splice
Die Index	15
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of	1
Crimps Required	
Plated	N
Plating Type	Unplated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splices
UPC	781810220467
UPC 12 Digit	7818102204677

## Dimensions

Dimension - B Length fraction	5/6 in
Dimension - B Length inch	0.83 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.89 in
Dimension - Outside Diameter inch	0.71 in

## Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> <li>• UL467</li> <li>• UL 486A-486B</li> <li>• IEEE 837</li> </ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"> <li>• UL467</li> <li>• UL 486A-486B</li> <li>• IEEE 837</li> </ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Pallet Quantity	9600

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YGHS\\_LineArt](#)
- [Sales Drawings - sd082513-01](#)
- [Specifications - YGHS26](#)