



## YGHS2C Compression Grounding Splice, 2 AWG Cu

By Burndy  
Catalog # YGHS2C



HYGROUND® Grounding Irreversible Compression Splice; Heavy Duty; Accommodates: #2 AWG

### General

Catalog Number	YGHS2C
Connector Type	Splice
Die Index	11
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Trade Name	HYLINK™
Type	Splices
UPC	781810220450
UPC 12 Digit	7818102204500

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.73 in
Dimension - Outside Diameter inch	0.50 in

### Conductor Related

Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	2 AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>UL467</li><li>UL 486A-486B</li><li>IEEE 837</li></ul>
Standards - Industry Standards Met	<ul style="list-style-type: none"><li>UL467</li><li>UL 486A-486B</li><li>IEEE 837</li></ul>
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	25
Pallet Quantity	24000

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YGHS\\_LineArt](#)
- [Sales Drawings - sd082513-01](#)
- [Specifications - YGHS2C](#)