

YGS34 Compression Grounding Splice, 500 kcmil Cu

By Burndy
Catalog # YGS34



HYGROUND® Grounding Irreversible Compression Splice;
Accommodates: 500 kcmil; 4.33" Length

General

| | |
|--|---------------|
| Catalog Number | YGS34 |
| Connector Type | Splice |
| Die Index | 20 |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 4 |
| Plated | N |
| Plating Type | Unplated |
| Trade Name | HYLINK™ |
| Type | Splices |
| UPC | 781810220443 |
| UPC 12 Digit | 7818102204433 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 2-1/5 in |
| Dimension - B Length inch | 2.20 in |
| Dimension - L Length Overall mm | 118 mm |
| Dimension - Length Overall inch | 4.63 in |
| Dimension - Outside Diameter inch | 1.06 in |

Conductor Related

| | |
|-----------------------------------|---------------|
| Conductor - Copper Str Size | 500 kcmil |
| Conductor - Copper Str Size Range | 500 kcmil |
| Conductor Type | CU C Str-Size |

Certifications And Compliance

| | |
|---|---|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | <ul style="list-style-type: none"> UL467 UL 486A-486B |
| Standards - Industry Standards Met | <ul style="list-style-type: none"> UL 486A-486B UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------|------|
| Carton Quantity | 6 |
| Pallet Quantity | 3456 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YGS_LineArt](#)
- [Sales Drawings - SD..082514-01](#)
- [Specifications - YGS34](#)