




# YH2929, Cu Compression H Tap, 250 kcmil-2 AWG Run and Tap

By Burndy  
Catalog # [YH2929](#)

Copper Compression H Tap, Tin Plated, Accommodating the following wire sizes - Run (Main): 250 kcmil-2 AWG Class B,C, 4/0 AWG-2 AWG Class I, DLO; Tap 1: 250 kcmil-2 AWG Class B,C, 4/0 AWG-2 AWG Class I, DLO. See sale drawing for metric wire size accommodates



## Application

Wire Tap

## General

Catalog Number	YH2929
Color Code	Purple
Connector Type	H-TAP
Die Index	654
EU RoHS Indicator	Yes
Finish Type	Tin-Plated
Material	COPPER
Plated	YES
Plating Type	Tin - Electro Plated
Sub Brand	CRIMPIT
Trade Name	HYLUG™
Type	Compression Taps
UPC	781810013830
UPC 12 Digit	7818100138300

## Dimensions

Dimension - Height inch	1.85 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.90 in
Dimension - Strip Length inch	1-1/16
Dimension - Width fraction	.90 in
Dimension - Width inch	1.85 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex G Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex G Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex G Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex H Run	4/0 AWG
Conductor - Copper Flex H Run Range	4/0 AWG
Conductor - Copper Flex H Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex H Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex I Run	4/0 AWG-2 AWG
Conductor - Copper Flex I Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex I Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex I Tap Range	4/0 AWG-2 AWG
Conductor - Copper Flex K Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex K Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex K Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex M Run Range	2 AWG-4/0 AWG
Conductor - Copper Flex M Tap	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Flex M Tap Range	2 AWG-4/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Tap	250 KCMIL-2 AWG

Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	50
Pallet Quantity	7200

### Product Assets

[3D Models - YH2929\\_MODEL-STEP](#)  
[3D Models - YH2929\\_MODEL-PDF](#)  
[3D Models - YH2929\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YH\\_LINEART](#)  
[Sales Drawings - SD..206566-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-YH2929-SPEC-EN | REV 6/2024