

YNS451R, ACSR - Jumper Loop Sleeve

By Burndy
Catalog # [YNS451R](#)



Al Tube Jumper Loop Sleeve, 840.2-927.2 kcmil(ACAR), 795-1000 kcmil(Al), 715.5-874.5 kcmil(ACSR), 10.04" L, For ACSR Cond.

Application

For ACSR And Stranded Aluminum Cable Up To And Including 230 KV

Starling kcmil;715.5 (30/19)
Redwing kcmil;795 (54/7)
Condor kcmil;795 (26/7) Drake
kcmil;795 (30/19) Mallard
kcmil;874.5 (54/7) Crane kcmil
715.5 (54/7) Crow kcmil-874.5
(54/7) Crane kcmil
795 kcmil;800 kcmil;874
kcmil;900 kcmil;954 kcmil;1000
kcmil
Conductor - AL Str Size Range 750 kcmil-1000 kcmil

General

Catalog Number	YNS451R
Connector Type	Splice
Construction Material - Main	Aluminum
Die Index	725
EU RoHS Indicator	Yes
Material	Aluminum
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YNS-R
UPC	781810094495
UPC 12 Digit	7818100944955

Conductor - ACSR Str Size Range

Conductor - AL Str Size

Conductor - AL Str Size Range

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Dimensions

Dimension - L Length Overall mm	255 mm
Dimension - Length Overall inch	10.04 in
Dimension - Outside Diameter inch	1.80 in

Conductor Related

Conductor - ACAR Str Size Range	840.2 kcmil-927.2 kcmil
Conductor - ACSR Str Size	715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7)

Logistics

Carton Quantity	10
Pallet Quantity	900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YNS-R_LINEART_BW](#)
[Sales Drawings - sd062800-01](#)
[Specifications - YNS451R](#)