



# YNT39R39R, Aluminum 2-piece T-Tap Connector

By Burndy  
Catalog # [YNT39R39R](#)



Compression T-Taps, ACCOM: 556.5 kcmil ACSR 600-650 kcmil  
ALUM INDEX: L722 T&B 125

## General

Catalog Number	YNT39R39R
Connector Type	Tap
Die Index	722
Material	Aluminum
UPC	781810136812
UPC 12 Digit	7818101368122

Conductor - ACSR Str Tap Range	kcmil;556.5 (30/7) Eagle kcmil-556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil
Conductor - AL Str Run	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Run Range	600 kcmil-650 kcmil
Conductor - AL Str Tap	600 kcmil;636 kcmil;650 kcmil
Conductor - AL Str Tap Range	600 kcmil-650 kcmil

## Dimensions

Dimension - B Length inch	4.47 in
Dimension - Height fraction	7-10/77 in
Dimension - Height inch	7.13 in
Dimension - Height mm	181.1 mm
Dimension - Length Overall inch	16.69 in
Dimension - Outside Diameter inch	1.5 in

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Conductor Related

Conductor - ACSR Str Size	556.5 (24/7) kcmil;556.5 (26/7) kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) kcmil-556.5 (26/7) kcmil
Conductor - ACSR Str Tap	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YNT-R-R\\_LINEART\\_BW](#)
- [Sales Drawings - SD65177-01](#)
- [Specifications - YNT39R39R](#)