



YP27AU26, Figure 3-shaped Aluminum Connector with adjustable spacer

By Burndy

Catalog # [YP27AU26](#)

Wide range, universal and reversible, Figure 3 shaped aluminum connector with adjustable overhanging spacer that separates conductors, Conductor Groove A Solid: 3/0, 4/0.



Features

- Wide range universal and reversible, Figure 3-shaped aluminum connector features adjustable overhanging spacer that separates conductors
- Spacer holds run or tap in place, permitting lineman to either approach the line ready to crimp or to assemble connector and tap on run and then crimp
- Massive aluminum design minimizes conductor corrosion due to galvanic action
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Copper, Aluminum Or ACSR Conductors

General

Catalog Number	YP27AU26
Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CABELOK CRIMPIT
Trade Name	CABELOK™ CRIMPIT™
Type	YP-U
UPC	781810134689
UPC 12 Digit	7818101346899

Dimensions

Dimension - Height inch	1.70 in
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	0.97 in

Conductor Related

Conductor - ACSR Str Size A	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size A Range	2/0 (6/1) Quail AWG

Conductor - ACSR Str Size B	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B Range	1 (6/1) Robin AWG-2/0 (6/1) Quail AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size B	1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Size B Range	1 AWG-2/0 AWG
Conductor - Copper Solid Size A	3/0 AWG;4/0 AWG
Conductor - Copper Solid Size A Range	3/0 AWG-4/0 AWG
Conductor - Copper Solid Size B	2/0 AWG;3/0 AWG
Conductor - Copper Solid Size B Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Size A	2/0 AWG;3/0 AWG
Conductor - Copper Str Size A Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Size B	1/0 ;2/0 AWG
Conductor - Copper Str Size B Range	1/0 -2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YPU_Lineart](#)
[Sales Drawings - sd045569-01](#)
[Specifications - YP27AU26](#)

