

YP2U3, Figure 3-shaped Aluminum Connector with adjustable spacer

By Burndy
Catalog # YP2U3



Wide range, universal and reversible, Figure 3 shaped aluminum connector with adjustable overhanging spacer that separates conductors, Conductor Groove A Solid: 6, 4, 3, 2.

Features

- Wide range universal and reversible, Figure 3-shaped aluminum connector features adjustable overhanging spacer that separates conductors
- Spacer holds run or tap in place, permitting lineman to either approach the line ready to crimp or to assemble connector and tap on run and then crimp
- Massive aluminum design minimizes conductor corrosion due to galvanic action
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Copper, Aluminum Or ACSR Conductors

General

Catalog Number	YP2U3
Die Index	O
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	CABELOK CRIMPIT
Trade Name	CABELOK™ CRIMPIT™
Type	YP-U
UPC	781810131732
UPC 12 Digit	7818101317322

Dimensions

Dimension - Height inch	1.30 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - Width inch	0.72 in

Conductor Related

Conductor - ACSR Str Size A	6 (6/1) Turkey AWG; 5 (6/1) Thrush AWG; 4 (6/1) Swan AWG; 4 (7/1) Swanate AWG
-----------------------------	---

Conductor - ACSR Str Size A Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG; 5 (6/1) Thrush AWG; 4 (6/1) Swan AWG; 4 (7/1) Swanate AWG
Conductor - ACSR Str Size B Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size A	6 AWG; 4 AWG
Conductor - AL Str Size A Range	6 AWG-4 AWG
Conductor - AL Str Size B	6 AWG; 4 AWG
Conductor - AL Str Size B Range	6 AWG-4 AWG
Conductor - Copper Solid Size A	6 AWG; 5 AWG; 4 AWG; 3 AWG; 2 AWG
Conductor - Copper Solid Size A Range	6 AWG-2 AWG
Conductor - Copper Solid Size B	6 AWG; 5 AWG; 4 AWG; 3 AWG; 2 AWG
Conductor - Copper Solid Size B Range	6 AWG-2 AWG
Conductor - Copper Str Size A	6 AWG; 5 AWG; 4 AWG; 3 AWG
Conductor - Copper Str Size A Range	6 AWG-3 AWG
Conductor - Copper Str Size B	6 AWG; 5 AWG; 4 AWG; 3 AWG
Conductor - Copper Str Size B Range	6 AWG-3 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[3D Models - YP2U3_MODEL-PDF](#)
[3D Models - YP2U3_MODEL-IGES](#)
[3D Models - YP2U3_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Interactive Catalog - BURNDY Full-Line Digital Catalog
Product Cross Section Image(s) - BUR_YPU_Lineart

Sales Drawings - sd045569-01
Specifications - YP2U3



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YP2U3-SPEC-EN | REV 10/2024