



## YPC28U26, Figure 6-shaped Connector

By Burndy

Catalog # [YPC28U26](#)

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:1/0-4/0.



## Features

- Extra wide range universal compression connector
- Figure 6-shape separates run and tap wires minimizes galvanic corrosion of conductors
- Connector can be gripped in tool and slipped over line for easy installation
- Pre-filled with PENETROX joint compound and stripsealed

## Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors

## General

Catalog Number	YPC28U26
Die Index	D3
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810136508
UPC 12 Digit	7818101365088

## Dimensions

Dimension - Height inch	2.06 in
Dimension - Height mm	52 mm
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in

## Conductor Related

Conductor - ACSR Str Run	1/0 AWG, 2/0 AWG,3/0 AWG,4/0 AWG
Conductor - ACSR Str Run Range	1/0 AWG-4/0 AWG
Conductor - ACSR Str Tap	6 AWG, 1/0 AWG
Conductor - ACSR Str Tap Range	6 AWG-1/0 AWG

Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	3 AWG-2/0 AWG
Conductor - Copper Str Run	1/0 AWG, 2/0 AWG, 3/0 AWG, 4/0 AWG
Conductor - Copper Str Run Range	1/0 AWG, 2/0 AWG, 3/0 AWG, 4/0 AWG
Conductor - Copper Str Tap	6 AWG, 2/0 AWG
Conductor - Copper Str Tap Range	6 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• CU C Solid-Run</li><li>• ACSR C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li><li>• CU C Solid-Tap</li><li>• ACSR C Str-Tap</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Product Assets

- [3D Models - YPC28U26\\_MODEL-IGES](#)
- [3D Models - YPC28U26\\_MODEL-STEP](#)
- [3D Models - YPC28U26\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YPCAU\\_Lineart](#)
- [Sales Drawings - sd042248-01](#)
- [Specifications - YPC28U26](#)

