



## YPC2A8U, Figure 6-shaped Connector

By Burndy  
Catalog # [YPC2A8U](#)

Compact compression connector designed to tap small lighting wires from secondaries. Figure 6-shape separates run and tap, and minimizes galvanic corrosion.



## Features

- Compact compression connector designed to tap small lighting wires from secondaries
- Figure 6-shape separates run and tap, minimizing galvanic corrosion
- Connector can be gripped in tool and slipped over line for easier installation
- Pre-filled with PENETROX joint compound and stripsealed

## Application

For Combinations Of Copper, Aluminum, ACSR, Compressed And Compact Conductors

## General

Catalog Number	YPC2A8U
Die Index	BG or 5/8
EU RoHS Indicator	Yes
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-A-U
UPC	781810135686
UPC 12 Digit	7818101356866

## Dimensions

Dimension - Height inch	0.97 in
Dimension - Height mm	25 mm
Dimension - L Length Overall mm	18 mm
Dimension - Length Overall inch	0.69 in
Dimension - Width inch	0.56 in

## Conductor Related

Conductor - ACSR Str Run	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-4 (7/1) Swanate AWG
Conductor - AL Str Run	6 AWG;4 AWG;3 AWG;2 AWG

Conductor - AL Str Run Range	6 AWG-2 AWG
Conductor - AL Str Tap	8 AWG
Conductor - Copper Solid Run	4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Run Range	4 AWG-2 AWG
Conductor - Copper Solid Tap	14 AWG
Conductor - Copper Str Run	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Run Range	6 AWG-2 AWG
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	14 AWG-8 AWG
Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• CU C Solid-Run</li><li>• ACSR C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li><li>• CU C Solid-Tap</li></ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Product Assets

- [3D Models - YPC2A8U\\_MODEL-PDF](#)
- [3D Models - YPC2A8U\\_MODEL-STEP](#)
- [3D Models - YPC2A8U\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YPCAU\\_Lineart](#)
- [Sales Drawings - sd055635-01](#)
- [Specifications - YPC2A8U](#)



A Hubbell brand