



YPC33R33R, Figure 6-shaped Connector

By Burndy

Catalog # [YPC33R33R](#)



Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run ACSR, 5005:266.8 (18-1) - 397.5 (18-1).

Features

- Extra wide range universal compression connector
- Figure 6-shape separates run and tap wires minimizes galvanic corrosion of conductors
- Connector can be gripped in tool and slipped over line for easy installation
- Pre-filled with PENETROX joint compound and stripsealed

Application

For Combinations Of Copper, Aluminum, ACSR, 6201, 5005 And Compressed And Compact Conductors

General

Catalog Number	YPC33R33R
Die Index	N
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YPC-U
UPC	781810138205
UPC 12 Digit	7818101382055

Dimensions

Dimension - Height inch	2.28 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.88 in
Dimension - Width inch	1.23 in

Conductor Related

Conductor - ACSR Str Run Range	266.8 kcmil-397.5 kcmil
Conductor - ACSR Str Tap Range	266.8 kcmil-397.5 kcmil
Conductor - AL Str Run	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil

Conductor - AL Str Run Range	250 kcmil-400 kcmil
Conductor - AL Str Tap	250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil
Conductor - AL Str Tap Range	250 kcmil-400 kcmil
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Run Range	250 kcmil-400 kcmil
Conductor - Copper Str Tap	250 kcmil;300 kcmil;350 kcmil;400 kcmil
Conductor - Copper Str Tap Range	250 kcmil-400 kcmil
Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• CU C Solid-Run• ACSR C Str-Run• AL C Str-Tap• CU C Str-Tap• CU C Solid-Tap• ACSR C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Product Assets

[3D Models - YPC33R33R_MODEL-STEP](#)
[3D Models - YPC33R33R_MODEL-IGES](#)
[3D Models - YPC33R33R_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YPCAU_Lineart](#)
[Sales Drawings - sd051577-01](#)
[Specifications - YPC33R33R](#)

