

Compression Splice

By Burndy
Catalog # YS29A1

AL Splice, AL9CU, Internal Chamfer, Tin Plated, Prefilled PENETROX™ A13 oxide inhibitor, End Cap, UL/CSA, 90°C, Up to 35kV, Color Code, Die Index.



Application

Wire Splice

General

Catalog Number	YS29A1
Color Code	Red
Connector Type	DUAL RATED
Die Index	324
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	ALUMINUM
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Temperature Rating	194
Trade Name	HYLINK™
Type	YS-A, Standard Barrel
UPC	781810757352
UPC 12 Digit	7818107573522

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.46 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - Outside Diameter inch	0.92 in
Dimension - Strip Length inch	1-5/8 in
Length	3.18 in
Outside Diameter	0.92 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - AL Str Size	250 KCMIL
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Compact Size	250
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	ALUMINUM / COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE
Wire Size	250 KCMIL

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[3D Models - YS29A1_MODEL-STEP](#)
[3D Models - YS29A1_MODEL-IGES](#)
[3D Models - YS29A1_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD..073942-01](#)

