

Compression Splice

By Burndy
Catalog # YS36L

600 kcmil CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GREEN Color Code, 22 or 472 Die Index.



Application

Wire Splice

General

| | |
|------------------------|-----------------------|
| Catalog Number | YS36L |
| Color Code | Green |
| Connector Type | STANDARD BARREL |
| Die Index | 22 |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLINK |
| Trade Name | HYLINK™ |
| Type | YS-L, Standard Barrel |
| UPC | 781810526408 |
| UPC 12 Digit | 7818105264088 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - B Length fraction | 1-3/8 in |
| Dimension - B Length inch | 1.38 in |
| Dimension - L Length Overall mm | 82 mm |
| Dimension - Length Overall inch | 3.22 in |
| Dimension - Strip Length inch | 1-7/16 |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|-------------------------------------|-----------|
| Conductor - Copper Str Compact Size | 600 |
| Conductor - Copper Str Size | 600 kcmil |
| Conductor - Material | COPPER |
| Conductor Size | 600 KCMIL |
| Conductor Type | CODE |
| Wire Size | 600 kcmil |

Certifications And Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------|---|
| Carton Quantity | 6 |
|-----------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD022390-01](#)