

# Compression Splice

By Burndy  
Catalog # [YS4CL](#)

4 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, GRAY Color Code, 8 or 346 Die Index.



## Application

Wire Splice

## General

Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK,SPLICE
Trade Name	HYLINK™
Type	YSL
UPC	781810070307
UPC 12 Digit	7818100703077

## Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Strip Length inch	7/8

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Compact Size	4
Conductor - Copper Str Size	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	200
Pallet Quantity	92800

## Product Assets

[3D Models - YS4CL\\_MODEL-IGES](#)  
[3D Models - YS4CL\\_MODEL-STEP](#)  
[3D Models - YS4CL\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD022390-01](#)