



# YS6CLBOX, Cu Compression Splice, Standard Barrel, 6 AWG

By Burndy  
Catalog # [YS6CLBOX](#)



6 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BLUE Color Code, 7 or 374 Die Index

## Application

Wire Splice

## General

Catalog Number	YS6CLBOX
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YS-L, Standard Barrel
UPC	781810555750
UPC 12 Digit	7818105557500

## Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Strip Length inch	7/8

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	6 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE
Wire Size	#6 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

[3D Models - YS6CLBOX\\_MODEL-PDF](#)  
[3D Models - YS6CLBOX\\_MODEL-STEP](#)  
[3D Models - YS6CLBOX\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd022390\\_1](#)



A proud member of the Hubbell Family.