

Compression Splice

By Burndy
Catalog # YSCM133

104,960 - 133,220 Circular Mils, CU, Internal Chamfer, Tin Plated, UL/CSA 90° Up to 35kV, Black Color Code, 13 Die Index.



Application

Wire Splice

General

Catalog Number	YSCM133
Color Code	Black
Connector Type	Splice
Die Index	13
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSCM
UPC	781810358559
UPC 12 Digit	7818103585599

Dimensions

Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.81 in
Dimension - Outside Diameter inch	0.64 in
Dimension - Strip Length inch	1-1/16

Electrical Ratings

Voltage - Maximum	600 V
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG
Conductor - Copper Str Size Range	1/0 -2/0 AWG
Conductor - Material	COPPER
Conductor Size	104,960-133,220 CMILS
Conductor Type	CODE
Wire Range	104,960 - 133,220 Circular Mils

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	200
Pallet Quantity	69600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section B - Small Compression](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094201](#)