

YSM6C, Uninsulated Parallel Splice For 10,380 - 26,813 cmils

By Burndy
Catalog # YSM6C



Copper Compression Parallel Splice, 10380-26813 Circular Mil,
0.44" Splice Length, Short Barrel, Tin Plated.

Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

General

Catalog Number	YSM6C
Connector Type	Parallel Splice
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Temperature Rating	90
Trade Name	HYLINK™
Type	YSM
UPC	781810805787
UPC 12 Digit	7818108057877

Dimensions

Dimension - Length Overall inch	0.44 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Strip Length inch	1/2

Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG
Conductor - Copper Solid Size Range	14 AWG-12 AWG
Conductor - Copper Str Size	14 AWG;12 AWG
Conductor - Copper Str Size Range	14 AWG-12 AWG
Conductor Size	10,380 - 26,813 cmils
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
-----------------	-----

Product Assets

[3D Models - YSM6C_MODEL-STEP](#)
[3D Models - YSM6C_MODEL-PDF](#)
[3D Models - YSM6C_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50094200](#)
[Specifications - YSM6C](#)