



YSR25FX2CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 1/0 Flex/AWG, Barrel B: 2 Flex/AWG

By Burndy
Catalog # YSR25FX2CFXLTKITC



CU Splice Reducer, Barrel A 1/0 Flex G,H,I,K,M,DLO, 1/0 AWG (B/C), Barrel B 2 Flex G,H,I,K,M,DLO, 2 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Pink/Brown Color Code, 12/10 Die Index.

Application

Wire Reducing Splice

General

Catalog Number	YSR25FX2CFXLTKITC
Color Code	Pink, Brown
Color Code - Side A	Pink
Color Code - Side B	Brown
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	12/10
Die Index - Element A	12
Die Index - Element B	10
Die Index Run Side	12
Die Index Tap Side	10
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810358313
UPC 12 Digit	7818103583133

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.04 in
Dimension - L Length Overall mm	54 mm
Dimension - Length BB inch	0.82 in
Dimension - Length Overall inch	2.19 in
Dimension - Strip Length inch	1.01 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	1/0 AWG
Conductor - Copper Flex G Size A	1/0 AWG
Conductor - Copper Flex G Size B	2 AWG
Conductor - Copper Flex G Tap	2 AWG
Conductor - Copper Flex H Run	1/0 AWG
Conductor - Copper Flex H Size A	1/0 AWG
Conductor - Copper Flex H Size B	2 AWG
Conductor - Copper Flex H Tap	2 AWG
Conductor - Copper Flex I Run	1/0 AWG
Conductor - Copper Flex I Size A	1/0 AWG
Conductor - Copper Flex I Size B	2 AWG
Conductor - Copper Flex I Tap	2 AWG
Conductor - Copper Flex K Run	1/0 AWG
Conductor - Copper Flex K Size A	1/0 AWG
Conductor - Copper Flex K Size B	2 AWG
Conductor - Copper Flex K Tap	2 AWG
Conductor - Copper Flex M Run	1/0 AWG
Conductor - Copper Flex M Size A	1/0 AWG
Conductor - Copper Flex M Size B	2 AWG
Conductor - Copper Flex M Tap	2 AWG
Conductor - Copper Str Size	1/0 AWG-2 AWG
Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	2 AWG
Conductor - Copper Str Size B Range	2 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG-2 AWG

Conductor Size	1/0 AWG-2 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG-2 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Pallet Quantity	2880

Product Assets

- [3D Models - YSR25FX2CFXLTCKITC_MODEL-PDF](#)
- [3D Models - YSR25FX2CFXLTCKITC_MODEL-STEP](#)
- [3D Models - YSR25FX2CFXLTCKITC_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Product Cross Section Image\(s\) - BUR_YSRKIT_Lineart](#)
- [Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.