



# YSR26FX6CFXLTCKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2/0 Flex/AWG, Barrel B: 6 Flex/AWG

By Burndy  
Catalog # YSR26FX6CFXLTCKITC



CU Splice Reducer, Barrel A 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, Barrel B 6 Flex G,H,I,K,M,DLO, 6 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Black/Blue Color Code, 13/7 Die Index.

## Application

Wire Reducing Splice

## General

Catalog Number	YSR26FX6CFXLTCKITC
Color Code	Black, Blue
Color Code - Side A	Black
Color Code - Side B	Blue
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	13/7
Die Index - Element A	13
Die Index - Element B	7
Die Index Run Side	13
Die Index Tap Side	7
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810345658
UPC 12 Digit	7818103456588

## Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.16 in
Dimension - L Length Overall mm	69 mm
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	2.71 in
Dimension - Strip Length inch	1.10 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Flex G Run	2/0 AWG
Conductor - Copper Flex G Size A	2/0 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper Flex G Tap	6 AWG
Conductor - Copper Flex H Run	2/0 AWG
Conductor - Copper Flex H Size A	2/0 AWG
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Flex H Tap	6 AWG
Conductor - Copper Flex I Run	2/0 AWG
Conductor - Copper Flex I Size A	2/0 AWG
Conductor - Copper Flex I Size B	6 AWG
Conductor - Copper Flex I Tap	6 AWG
Conductor - Copper Flex K Run	2/0 AWG
Conductor - Copper Flex K Size A	2/0 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex K Tap	6 AWG
Conductor - Copper Flex M Run	2/0 AWG
Conductor - Copper Flex M Size A	2/0 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Flex M Tap	6 AWG
Conductor - Copper Str Size	2/0 AWG-6 AWG
Conductor - Copper Str Size A	6 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG-6 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG-6 AWG

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	12
Pallet Quantity	2880

### Product Assets

[3D Models - YSR26FX6CFXLTKITC\\_MODEL-STEP](#)  
[3D Models - YSR26FX6CFXLTKITC\\_MODEL-IGES](#)  
[3D Models - YSR26FX6CFXLTKITC\\_MODEL-PDF](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - SPLICE KIT trilingual](#)  
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY\_MX-YSR26FX6CFXLTKITC-SPEC-EN | REV 6/2024