



YSR2CFX6CFXLTCKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2 Flex/AWG, Barrel B: 6 Flex/AWG

By Burndy
Catalog # YSR2CFX6CFXLTCKITC



CU Splice Reducer, Barrel A 2 Flex G,H,I,K,M,DLO, 2 AWG, Barrel B 6 Flex G,H,I,K,M,DLO, 6 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Brown/Blue Color Code, 10/7 Die Index.

Application

Wire Reducing Splice

General

Catalog Number	YSR2CFX6CFXLTCKITC
Color Code	Brown, Gray
Color Code - Side A	Brown
Color Code - Side B	Blue
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	10/7
Die Index - Element A	10
Die Index - Element B	7
Die Index Run Side	10
Die Index Tap Side	7
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810345764
UPC 12 Digit	7818103457644

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.82 in
Dimension - L Length Overall mm	50 mm
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	1.96 in
Dimension - Strip Length inch	0.78 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	2 AWG
Conductor - Copper Flex G Size A	2 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper Flex G Tap	6 AWG
Conductor - Copper Flex H Run	2 AWG
Conductor - Copper Flex H Size A	2 AWG
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Flex H Tap	6 AWG
Conductor - Copper Flex I Run	2 AWG
Conductor - Copper Flex I Size A	2 AWG
Conductor - Copper Flex I Size B	6 AWG
Conductor - Copper Flex I Tap	6 AWG
Conductor - Copper Flex K Run	2 AWG
Conductor - Copper Flex K Size A	2 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex K Tap	6 AWG
Conductor - Copper Flex M Run	2 AWG
Conductor - Copper Flex M Size A	2 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Flex M Tap	6 AWG
Conductor - Copper Str Size	2 AWG-6 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG-6 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG-6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	2250

Product Assets

- [3D Models - YSR2CFX6CFXLTKITC_MODEL-PDF](#)
- [3D Models - YSR2CFX6CFXLTKITC_MODEL-STEP](#)
- [3D Models - YSR2CFX6CFXLTKITC_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.