



YSR2CFX8CFXLTCKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2 Flex/AWG, Barrel B: 8 Flex/AWG

By Burndy
Catalog # YSR2CFX8CFXLTCKITC



CU Splice Reducer, Barrel A 2 Flex G,H,I,K,M,DLO, 2 AWG, Barrel B 8 Flex G,H,I,K,M,DLO, 8 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Brown/Red Color Code, 10/49 Die Index.

Application

Wire Reducing Splice

General

Catalog Number	YSR2CFX8CFXLTCKITC
Color Code	Brown, Red
Color Code - Side A	Brown
Color Code - Side B	Red
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	10/49
Die Index - Element A	10
Die Index - Element B	49
Die Index Run Side	10
Die Index Tap Side	49
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810473948
UPC 12 Digit	7818104739488

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.82 in
Dimension - L Length Overall mm	45 mm
Dimension - Length BB inch	0.60 in
Dimension - Length Overall inch	2.02 in
Dimension - Strip Length inch	0.78 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	2 AWG
Conductor - Copper Flex G Size A	2 AWG
Conductor - Copper Flex G Size B	8 AWG
Conductor - Copper Flex G Tap	8 AWG
Conductor - Copper Flex H Run	2 AWG
Conductor - Copper Flex H Size A	2 AWG
Conductor - Copper Flex H Size B	8 AWG
Conductor - Copper Flex H Tap	8 AWG
Conductor - Copper Flex I Run	2 AWG
Conductor - Copper Flex I Size A	2 AWG
Conductor - Copper Flex I Size B	8 AWG
Conductor - Copper Flex I Tap	8 AWG
Conductor - Copper Flex K Run	2 AWG
Conductor - Copper Flex K Size A	2 AWG
Conductor - Copper Flex K Size B	8 AWG
Conductor - Copper Flex K Tap	8 AWG
Conductor - Copper Flex M Run	2 AWG
Conductor - Copper Flex M Size A	2 AWG
Conductor - Copper Flex M Size B	8 AWG
Conductor - Copper Flex M Tap	8 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Str Size	2 AWG-8 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG-8 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG-8 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	6000

Product Assets

[3D Models - YSR2CFX8CFXLTKITC_MODEL-IGES](#)
[3D Models - YSR2CFX8CFXLTKITC_MODEL-PDF](#)
[3D Models - YSR2CFX8CFXLTKITC_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.