



Compression Splice Reducer

By Burndy
Catalog # YSR3128LTCKITC

CU Splice Reducer, Barrel A 350 kcmil, Barrel B 4/0 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Red/Purple Color Code, 18/15 Die Index.



Application

Wire Reducing Splice

General

Catalog Number	YSR3128LTCKITC
Color Code	Red, Purple
Color Code - Side A	Red
Color Code - Side B	Purple
Connector Type	STANDARD BARREL KITS
Die Index	18/15
Die Index - Element A	18
Die Index - Element B	15
Die Index Run Side	18
Die Index Tap Side	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™
UPC	781810345290
UPC 12 Digit	7818103452900

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.49 in
Dimension - L Length Overall mm	83 mm
Dimension - Length BB inch	1.30 in
Dimension - Length Overall inch	3.27 in
Dimension - Strip Length inch	1.41 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	350 KCMIL-4/0 AWG
Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	350 KCMIL-4/0 AWG
Conductor Type	CODE
Wire Size	350 KCMIL-4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Pallet Quantity	1080

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YSR3128LTCKITC-SPEC-EN | REV 6/2024

