



Compression Splice Reducer

By Burndy
Catalog # [YSR44FX29FXLTCKITC](#)

CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 250 kcmil, 4/0 G,H,I,K,M,DLO, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Yellow/Yellow Color Code, L115/16 Die Index.



Application

Wire Reducing Splice

General

Catalog Number	YSR44FX29FXLTCKITC
Color Code	Yellow, Yellow
Color Code - Side A	Yellow
Color Code - Side B	Yellow
Connector Type	STANDARD BARREL KITS
Die Index	L115/16
Die Index - Element A	L115
Die Index - Element B	16
Die Index Run Side	L115
Die Index Tap Side	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
UPC	781810472286
UPC 12 Digit	7818104722866

Dimensions

Dimension - B Length fraction	2-1/16 in
Dimension - B Length inch	2.09 in
Dimension - L Length Overall mm	135 mm
Dimension - Length BB inch	1.44 in
Dimension - Length Overall inch	5.33 in
Dimension - Strip Length inch	1.96 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex H Run	750 KCMIL
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Flex I Size A	750 KCMIL
Conductor - Copper Flex I Size A Range	750 KCMIL
Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex K Size B Range	4/0 AWG
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex M Run	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Flex M Size B Range	4/0 AWG
Conductor - Copper Flex M	4/0 AWG

Tap	
Conductor - Copper Str Size	750 KCMIL-250 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Material	COPPER
Conductor Size	750 KCMIL-250 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL-250 KCMIL

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12
Pallet Quantity	396

Product Assets

- [3D Models - YSR44FX29FXLTCKITC_MODEL-IGES](#)
- [3D Models - YSR44FX29FXLTCKITC_MODEL-STEP](#)
- [3D Models - YSR44FX29FXLTCKITC_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - SPLICE KIT trilingual](#)
- [Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.