



YSR4CFX6CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink,

By Burndy
Catalog # YSR4CFX6CFXLTKITC

Cu Splice Reducer, Barrel A 4 Flex G,H,I,K,M,DLO, 4 AWG, Barrel B 6 Flex G,H,I,K,M,DLO, 6 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Gray/Blue Color Code, 8/7 Die Index.



Application

Wire Reducing Splice

General

Catalog Number	YSR4CFX6CFXLTKITC
Color Code	Gray, Blue
Color Code - Side A	Gray
Color Code - Side B	Blue
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	8/7
Die Index - Element A	8
Die Index - Element B	7
Die Index Run Side	8
Die Index Tap Side	7
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810345801
UPC 12 Digit	7818103458011

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.74 in
Dimension - L Length Overall mm	42 mm
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	1.67 in
Dimension - Strip Length inch	0.71 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	4 AWG
Conductor - Copper Flex G Size A	4 AWG
Conductor - Copper Flex G Size A Range	4 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper Flex G Size B Range	6 AWG
Conductor - Copper Flex G Tap	6 AWG
Conductor - Copper Flex H Run	4 AWG
Conductor - Copper Flex H Size A	4 AWG
Conductor - Copper Flex H Size A Range	4 AWG
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Flex H Size B Range	6 AWG
Conductor - Copper Flex H Tap	6 AWG
Conductor - Copper Flex I Run	4 AWG
Conductor - Copper Flex I Size A	4 AWG
Conductor - Copper Flex I Size A Range	4 AWG
Conductor - Copper Flex I Size B	6 AWG
Conductor - Copper Flex I Size B Range	6 AWG
Conductor - Copper Flex I Tap	6 AWG
Conductor - Copper Flex K Run	4 AWG
Conductor - Copper Flex K Size A	4 AWG
Conductor - Copper Flex K Size A Range	4 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex K Size B Range	6 AWG
Conductor - Copper Flex K Tap	6 AWG
Conductor - Copper Flex M	4 AWG

Run	
Conductor - Copper Flex M Size A	4 AWG
Conductor - Copper Flex M Size A Range	4 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Flex M Size B Range	6 AWG
Conductor - Copper Flex M Tap	6 AWG
Conductor - Copper Str Run Range	4 AWG
Conductor - Copper Str Size	4 AWG-6 AWG
Conductor - Copper Str Size B	6 AWG
Conductor - Copper Str Tap Range	6 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG-6 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG-6 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Pallet Quantity	3600

Product Assets

[3D Models - YSR4CFX6CFXLTCKITC_MODEL-IGES](#)
[3D Models - YSR4CFX6CFXLTCKITC_MODEL-STEP](#)
[3D Models - YSR4CFX6CFXLTCKITC_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YSR4CFX6CFXLTCKITC-SPEC-EN | REV 6/2024