



YSR6CFX8CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink,

By Burndy
Catalog # YSR6CFX8CFXLTKITC

Cu Splice Reducer, Barrel A 6 Flex G,H,I,K,M,DLO, 6 AWG, Barrel B 8 Flex G,H,I,K,M,DLO, 8 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink, Blue/Red Color Code, 7/49 Die Index.



Application

Wire Reducing Splice

General

Catalog Number	YSR6CFX8CFXLTKITC
Color Code	Blue, Red
Color Code - Side A	Blue
Color Code - Side B	Red
Connector Type	STANDARD BARREL KITS
Construction Material - Main	Copper
Die Index	7/49
Die Index - Element A	7
Die Index - Element B	49
Die Index Run Side	7
Die Index Tap Side	49
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYREDUCER™
Type	YSR-TC
UPC	781810473924
UPC 12 Digit	7818104739244

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.73 in
Dimension - L Length Overall mm	35 mm
Dimension - Length BB inch	0.60 in
Dimension - Length Overall inch	1.37 in
Dimension - Strip Length inch	0.70 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Run	6 AWG
-------------------------------	-------

Conductor - Copper Flex I Size A	6 AWG
Conductor - Copper Flex I Size A Range	6 AWG
Conductor - Copper Flex I Size B	8 AWG
Conductor - Copper Flex I Size B Range	8 AWG
Conductor - Copper Flex I Tap	8 AWG
Conductor - Copper Flex K Run	6 AWG
Conductor - Copper Flex K Size A	6 AWG
Conductor - Copper Flex K Size A Range	6 AWG
Conductor - Copper Flex K Size B	8 AWG
Conductor - Copper Flex K Size B Range	8 AWG
Conductor - Copper Flex K Tap	8 AWG
Conductor - Copper Flex M Run	6 AWG
Conductor - Copper Flex M Size A	6 AWG
Conductor - Copper Flex M Size A Range	6 AWG
Conductor - Copper Flex M Size B	8 AWG
Conductor - Copper Flex M Size B Range	8 AWG
Conductor - Copper Flex M Tap	8 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Str Run Range	6 AWG
Conductor - Copper Str Size	6 AWG-8 AWG
Conductor - Copper Str Size B	8 AWG
Conductor - Copper Str Tap Range	8 AWG
Conductor - Material	COPPER
Conductor Size	6 AWG-8 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG-8 AWG

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Conductor - Copper Flex G Size A 6 AWG
Conductor - Copper Flex G Size A Range 6 AWG
Conductor - Copper Flex G Size B 8 AWG
Conductor - Copper Flex G Size B Range 8 AWG
Conductor - Copper Flex G Tap 8 AWG
Conductor - Copper Flex H Run 6 AWG
Conductor - Copper Flex H Size A 6 AWG
Conductor - Copper Flex H Size A Range 6 AWG
Conductor - Copper Flex H Size B 8 AWG
Conductor - Copper Flex H Size B Range 8 AWG
Conductor - Copper Flex H Tap 8 AWG
Conductor - Copper Flex I Run 6 AWG

Certification - ETL No
Certification - UL Recognized No
Certification - cULus No
Standards - RoHS Compliance CM
Status
UL Listed No

Logistics

Carton Quantity 25
Pallet Quantity 6000

Product Assets

[3D Models - YSR6CFX8CFXLTCKITC_MODEL-IGES](#)
[3D Models - YSR6CFX8CFXLTCKITC_MODEL-STEP](#)
[3D Models - YSR6CFX8CFXLTCKITC_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - SPLICE KIT trilingual](#)
[Sales Drawings - 10021428](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY_MX-YSR6CFX8CFXLTCKITC-SPEC-EN | REV 6/2024