

Compression T-Connector

By Burndy
Catalog # YST2525

Cu compression T-Coupler, 1/Ostr(Run), 1/Ostr(Tap), Pink(Run&Tap), 12(Run&Tap) Index.



Application

T-Connector

General

Catalog Number	YST2525
Color Code	Pink
Color Code - Side A	Pink
Color Code - Side B	Pink
Connector Type	T-COUPLER
Die Index	12/12
Die Index Run Side	12
Die Index Tap Side	12
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810001134
UPC 12 Digit	7818100011344

Dimensions

Dimension - A Outside Diameter inch	0.51 in
Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - B Outside Diameter inch	0.51 in
Dimension - Height inch	1.91 in
Dimension - L Length Overall mm	97 mm
Dimension - Length BB inch	1.56 in
Dimension - Length Overall inch	3.81 in
Dimension - Width inch	1.56 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	1/0 AWG
Conductor - Copper Str Run Range	1/0 AWG
Conductor - Copper Str Tap	1/0 AWG
Conductor - Copper Str Tap Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG-1/0 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Pallet Quantity	11600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YST_LineArt](#)
[Sales Drawings - 238867](#)

