

Compresson T-Connector

By Burndy
Catalog # YST2C2C

Cu compression T-Coupler, 2 str(Run&Tap), 600V-35Kv, Tin plated, Brown,10 index.



Application

T-Connector

General

Catalog Number	YST2C2C
Color Code	Brown
Color Code - Side A	Brown
Color Code - Side B	Brown
Connector Type	T-COUPLER
Die Index	10/10
Die Index Run Side	10
Die Index Tap Side	10
EU RoHS Indicator	Yes
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYTEE
Temperature Rating	194
Trade Name	HYTEE™
Type	YST, Uninsulated T
UPC	781810501108
UPC 12 Digit	7818105011088

Dimensions

Dimension - A Outside Diameter inch	0.42 in
Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - B Outside Diameter inch	0.42 in
Dimension - Height inch	1.98 in
Dimension - L Length Overall mm	90 mm
Dimension - Length BB inch	1.56 in
Dimension - Length Overall inch	3.56 in
Dimension - Width inch	1.50 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	2 AWG
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG-2 AWG
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	14800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YST_LineArt](#)
[Sales Drawings - 2388605](#)

