



# Compression T-Connector

By Burndy  
Catalog # [YST4C4C](#)



UNINSULATED HIGH VOLTAGE COPPER COMPRESSION  
SPLICE STANDARD BARREL-TAPERED ENDS.

## Application

T-Connector

## General

Catalog Number	YST4C4C
Color Code	Gray
Color Code - Side A	Gray
Color Code - Side B	Gray
Connector Type	T-COUPLER
Die Index	8/8
Die Index Run Side	8
Die Index Tap Side	8
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYTEE™
UPC	781810501153
UPC 12 Digit	7818105011533

## Dimensions

Dimension - A Outside Diameter inch	0.34 in
Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - B Outside Diameter inch	0.34 in
Dimension - Height inch	1.72 in
Dimension - L Length Overall mm	83 mm
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.25 in
Dimension - Width inch	1.38 in

## Electrical Ratings

Voltage - Maximum 35000

## Conductor Related

Conductor - Copper Str Run	4 AWG
Conductor - Copper Str Run Range	4 AWG
Conductor - Copper Str Tap	4 AWG
Conductor - Copper Str Tap Range	4 AWG
Conductor - Material	COPPER
Conductor Size	4 AWG-4 AWG
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Pallet Quantity	24000

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YST\\_LineArt](#)  
[Sales Drawings - SE..023886-03](#)



A proud member of the Hubbell Family.

