

YSV25FXB, Compression Splice, 1/0 AWG

By Burndy
Catalog # YSV25FXB



Compression Splice, 1/0 AWG, 600 - 35000 V, 3.18 IN L, Die Index: 12.

Application

For Higher voltage applications

General

Catalog Number	YSV25FXB
Color Code	Pink
Connector Type	Splice
Die Index	12
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810041451

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - D inch	0.66 in
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Strip Length inch	1-9/16 in

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24) DLO
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Solid Size	1/0 AWG
Conductor - Copper Str Compact Size	1/0
Conductor - Copper Str Compact Size Range	1/0
Conductor - Copper Str Navy Size	100 (61)
Conductor - Copper Str Size	1/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE208037-01_F](#)
- [Specifications - BURNDY_YSV25FXB_Specsheet](#)