

YSV27FXB, Compression Splice, 3/0 Flex

By Burndy
Catalog # YSV27FXB



Copper Compression Splice, 3/0 Flex, 3.46" Splice Length, Long Barrel, Belled End, Tin Plated

General

Catalog Number	YSV27FXB
Color Code	Orange
Connector Type	Splice
Die Index	14
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLINK™
Type	Splice
UPC	781810041475

Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Solid Size	3/0 AWG
Conductor - Copper Str Compact Size	3/0
Conductor - Copper Str Compact Size Range	3/0
Conductor - Copper Str Navy Size	150 (61)
Conductor - Copper Str Size	3/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.64 in
Dimension - D inch	0.82 in
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.46 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Strip Length inch	1-11/16 in

Conductor Related

Conductor - Copper DLO Size	3/0 (450/#24) DLO
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE208037-01_F](#)
- [Specifications - BURNDY_YSV27FXB_Specsheet](#)
- [Specifications - YSV27FXB](#)