

## YSV2CFXB, Compression Splice, #2 Str AWG

By Burndy

Catalog # [YSV2CFXB](#)



Cu Compression Belled End Splice, #2 STR AWG, 600 V to 35 KV, Long Barrel, Brown, 10 Index

### General

Catalog Number	YSV2CFXB
Color Code	Brown
Connector Type	Splice
Die Index	10
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
Type	Splice
UPC	781810099919

Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Compact Size	2
Conductor - Copper Str Compact Size Range	2
Conductor - Copper Str Navy Size	60 (37)
Conductor - Copper Str Size	2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.35 in
Dimension - D inch	0.54 in
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.89 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Strip Length inch	1-7/16 in

### Conductor Related

Conductor - Copper DLO Size	2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SE208037-01\\_F](#)
- [Specifications - YSV2CFXB](#)
- [Specifications - BURNDY\\_YSV2CFXB\\_Specsheet](#)