

YSV2CL, Uninsulated Splice For 2 AWG

By Burndy
Catalog # [YSV2CL](#)



HYLINK™ Uninsulated Compression Butt Splice; Seamless Standard Barrel; Accommodates: #2 AWG Str/Sol, AN, Aircraft; Length: 1.41" ; 600 V Max; Bulk Package

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For Aircraft, Light Duty Industrial And General Purpose Applications

General

Catalog Number	YSV2CL
Connector Type	Seamless Butt Splice
Die Index	41
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	Chamfered
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	Splice
UPC	781810543894

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - L Length Overall mm	36 mm
Dimension - Length Overall inch	1.41 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Strip Length inch	5/8 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Aircraft Size	AN 2
Conductor - Copper Str Size	2 AWG
Conductor Size	2 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	200
Pallet Quantity	69600

Product Assets

[3D Models - YSV2CL_MODEL-STEP](#)
[3D Models - YSV2CL_MODEL-IGES](#)
[3D Models - YSV2CL_MODEL-PDF](#)
[Catalogs - BURNDY Master Catalog - Section B - Small Compression](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YSV-L_LineArt](#)
[Sales Drawings - 50094198](#)
[Specifications - YSV2CL](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY_MX-YSV2CL-SPEC-EN | REV 10/2024