



Kellems Wire Management, Deluxe Cord Grips, Straight Male 1.250-1.375", 2" with Mesh

By Bryant
Catalog # 074011258

Kellems Wire Management, Deluxe Cord Grips, Straight Male 1.250- 1.375", 2" with Mesh



Features

- Stainless steel mesh is corrosion resistant
- Multiweave grip gives cable arc-of-bend control
- Endless weave provides easy cable/flexible conduit installation

Application

Straight Male- Form 6

General

Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Item Type	Deluxe Cord Grips
Material	Aluminum Fittings, Stainless Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	<ul style="list-style-type: none">• Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2(Fitting)• Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C• Environmental - Operating Temperatures - -30°F to +240°F (-34°C to +115°C)• Environmental - Wet Locations - Suitable for use in wet locations when used with a listed sealing ring between box and fitting
Series	Deluxe Cord Grips
Style	For Insulated Cables
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Thread Size	2" NPT
Type	Straight Male Thread
UPC	783585330860

Dimensions

Display Size	2" NPT
--------------	--------

Conductor Related

Cable Diameter Range	1.250 in-1.375 in
Cable Size	1.250"-1.375" (3.17-3.49)
Conductor Range	1.25-1.375 in (3.17-3.49 mm)
Number Of Conductors	Single

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Literature - Wire Management Solutions Brochure](#)
[Sales Drawings - WDK_074011258_DRAWING_PDF](#)



A proud member of the Hubbell Family.