



**Straight Blade Devices,  
Receptacles, Quad-PLEX,  
Commercial/Industrial Grade, 15A  
125V, 2-Pole 3-Wire Grounding, 5-  
15R, Brown, Single Pack**

By Bryant  
Catalog # 1254B



Straight Blade Devices, Receptacles, Quad-PLEX,  
Commercial/Industrial Grade, 15A 125V, 2-Pole 3-Wire  
Grounding, 5-15R, Brown, Single Pack

**General**

Application	Commercial/Industrial
Catalog Number	1254B
Color	Brown
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Type	Four Outlet Receptacle
UPC	781786336254

**Dimensions**

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.4 lb
Width	4.3 in

**Electrical Ratings**

Amperage Rating	15 A
Connectivity	Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

**Conductor Related**

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

**Certifications And Compliance**

Nema Rating	5-15R
-------------	-------

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

[Catalog Page - BRY A-15 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-1254B-SPEC-EN | REV 6/2024