



Straight Blade Devices,
Receptacles, Quad-PLEX,
Commercial/Industrial Grade,
Isolated Ground, 15A 125V, 2-Pole
3-Wire Grounding, 5-15R, Bulk
Package

By Bryant
Catalog # 1254IGOB



Straight Blade Devices, Receptacles, Quad-PLEX,
Commercial/Industrial Grade, Isolated Ground, 15A 125V, 2-
Pole 3-Wire Grounding, 5-15R, Orange, Bulk Package

Application

Commercial/Industrial

General

Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Type	Four Outlet Receptacle
UPC	781786336322

Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.45 lb
Width	4.3 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY A-15 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.