



Locking Devices, Bryant Power Interrupting, Flanged Inlet, 30A 3-Phase Delta 480V AC, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted

By Bryant
Catalog # 20418



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 30A 600V AC/20A 250V DC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

Application

Extra Heavy Duty Industrial Specification Grade

General

Catalog Number	20418
Color	Aluminum
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	20A/30A Flanged Inlet
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Flanged Inlet
UPC	781786618527

Dimensions

Dimensions	3.28 in x 1.94 in x 1.75 in
Display Size	Standard Sized Product
Height	1.75 in
Length	3.28 in
Width	1.94 in

Electrical Ratings

Amperage Rating	20A/30 A
Connectivity	Terminal Screws
Current Rating	20A/30 A
Phase	Single Phase
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - BRY H-25 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)
[Specifications - 20418](#)