



# Locking Devices, Bryant Power Interrupting, Flanged Inlet, 30A 3-Phase Delta 480V AC, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted

By Bryant  
Catalog # 20418



Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 30A 600V AC/20A 250V DC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted

## Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

## Application

Extra Heavy Duty Industrial Specification Grade

## General

|                              |   |
|------------------------------|---|
| Catalog Number               | 20418   |
| Color                        | Aluminum  |
| EU RoHS Indicator            | No  |
| Environmental Conditions     | Indoor Dry Unless Protected By Additional Means |
| Item Type                    | 20A/30A Flanged Inlet                           |
| Material                     | Composite                                       |
| Material - Mounting Hardware | Screw Mounting                                  |
| Number Of Poles              | 3-Pole  |
| OEM Brand Name               | Hubbell Bryant                                  |
| Style                        | Grounding                                       |
| Type                         | Flanged Inlet                                   |
| UPC                          | 781786618527                                    |

## Dimensions

|              |                             |
|--------------|-----------------------------|
| Dimensions   | 3.28 in x 1.94 in x 1.75 in |
| Display Size | Standard Sized Product      |
| Height       | 1.75 in                     |
| Length       | 3.28 in                     |
| Width        | 1.94 in                     |

## Electrical Ratings

|                            |                 |
|----------------------------|-----------------|
| Amperage Rating            | 20A/30 A        |
| Connectivity               | Terminal Screws |
| Current Rating             | 20A/30 A        |
| Phase                      | Single Phase    |
| Voltage Rating             | 250 VDC/600 VAC |
| Voltage Rating Description | 250 VDC/600 VAC |

## Conductor Related

|                 |                   |
|-----------------|-------------------|
| Number Of Wires | 4-Wire            |
| Wire Size       | #18 AWG to #8 AWG |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

## Product Assets

[Catalog Page - BRY H-25 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 20418](#)