



# Straight Blade Devices, Receptacles, Quad-PLEX, Hospital Grade, Isolated Ground, 20A 125V, 2 -Pole 3-Wire Grounding, 5-20R, Orange, Single Pack

By Bryant  
Catalog # 21254HIGO



Straight Blade Devices, Receptacles, Quad-PLEX, Hospital Grade, Isolated Ground, 20A 125V, 2 -Pole 3-Wire Grounding, 5-20R, Orange, Single Pack

## General

Application	Hospital Grade
Catalog Number	21254HIGO
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hospital Grade
Type	Four Outlet Receptacle
UPC	781786336803

## Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.4 lb
Width	4.3 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - BRY B-5 Catalog Page](#)
- [Catalog Page - BRY A-6 Catalog Page](#)
- [Catalog Page - BRY A-15 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Healthcare Solutions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRY-21254HIGO-SPEC-EN | REV 6/2024