



Straight Blade Devices,  
Receptacles, Quad-PLEX, Hospital  
Grade, Isolated Ground, 20A 125V, 2  
-Pole 3-Wire Grounding, 5-20R,  
Orange, Single Pack

By Bryant  
Catalog # 21254HIGO

Straight Blade Devices, Receptacles, Quad-PLEX, Hospital Grade,  
Isolated Ground, 20A 125V, 2 -Pole 3-Wire Grounding, 5-20R,  
Orange, Single Pack

Features

- Quad-PLEX
- Hospital Grade
- Isolated Ground
- 20A 125V
- 2 -Pole 3-Wire Grounding

Application

Hospital Grade

General

Catalog Number	21254HIGO
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Smooth Face
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Hospital Grade
Type	Four Outlet Receptacle
UPC	781786336803

Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in



Weight	0.4 lb
Width	4.3 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY B-5 Catalog Page](#)
- [Catalog Page - BRY A-6 Catalog Page](#)
- [Catalog Page - BRY A-15 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Literature - General Literature - Healthcare Solutions](#)
- [Specifications - 21254HIGO](#)