



# Straight Blade Devices, Receptacles, Quad-PLEX, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack

By Bryant  
Catalog # 21254I



Straight Blade Devices, Receptacles, Quad-PLEX, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory, Single Pack

## Features

- Quad-PLEX
- Commercial/Industrial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

## Application

Commercial/Industrial

## General

Catalog Number	21254I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Quad-Plex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Four Outlet Receptacle
UPC	781786336582

## Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in

Length	4.3 in
Weight	0.35 lb
Width	4.3 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY A-15 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 21254I](#)

