



# Straight Blade Devices, Receptacles, Quad-PLEX, Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Single Pack, Isolated Ground

By Bryant  
Catalog # 21254IGO



Straight Blade Devices, Receptacles, Quad-PLEX,  
Commercial/Industrial Grade, 20A 125V, 2-Pole 3-Wire  
Grounding, 5-20R, Orange, Single Pack, Isolated Ground

## Features

- Quad-PLEX
- Commercial/Industrial Grade
- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R

## Application

Commercial/Industrial

## General

Catalog Number	21254IGO
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Quad-Plex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Straight Blade
Style	4-Receptacle
Type	Four Outlet Receptacle
UPC	781786336636

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications And Compliance

Nema Rating	5-20R
Standards - RoHS Compliance	CM
Status	

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - BRY D-6 Catalog Page](#)  
[Catalogs - Bryant Full Line Catalog](#)  
[Specifications - 21254IGO](#)

