



Straight Blade Devices, Receptacles, Quad-PLEX, Commercial/Industrial Grade, Isolated Ground, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Single Pack

By Bryant
Catalog # 21254IGOL



Straight Blade Devices, Receptacles, Quad-PLEX,
Commercial/Industrial Grade, Isolated Ground, 20A 125V, 2-
Pole 3-Wire Grounding, 5-20R, Orange, Single Pack

Application

Commercial/Industrial

General

Color	Orange
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Quad-Plex
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Series	Commercial
Style	Smooth Face
Type	Four Outlet Receptacle
UPC	781786336728

Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.45 lb
Width	4.3 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Wire Leads
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - BRY D-6 Catalog Page](#)
[Catalog Page - BRY A-15 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRY-21254IGOL-SPEC-EN | REV 5/2024