




**Straight Blade Devices,
Receptacles, QUADPLEX
Receptacle, Surge Suppression,
Isolated Ground, Wire Leads, 20A
125V, 2-Pole 3-Wire Grounding, 5-
20R**



By Bryant
Catalog # [21254SILA](#)

Straight Blade Devices, Receptacles, QUADPLEX Receptacle, Surge Suppression, Isolated Ground, Wire Leads, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

Features

- QUADPLEX Receptacle
- Surge Suppression
- Isolated Ground
- Wire Leads
- 20A 125V

Application

Quad-Plex

General

Catalog Number	21254SILA
Color	Ivory
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Visual Status Indicator
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Number Of Outlets	4
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Commercial
Style	Smooth Face
Type	Four Outlet Receptacle
UPC	781786190351

Dimensions

Dimensions	4.3 in x 4.30 in x 0.92 in
Display Size	Standard Sized Product
Height	0.92 in
Length	4.3 in
Weight	0.4 lb
Width	4.3 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Wire Leads
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - BRY D-3 Catalog Page](#)
- [Catalog Page - BRY A-15 Catalog Page](#)
- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - 21254SILA](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-21254SILA-SPEC-EN | REV 10/2024