



# Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 30A 250V DC/600V AC, Non-NEMA

By Bryant  
Catalog # 21414

Locking Devices, Bryant Power Interrupting, Industrial, Female Connector Body, 30A 600V AC/ 20A 250V DC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Black nylon with cord grip



## Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

## Application

Heavy Duty Industrial

## General

Color	Black, White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A/30A Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	Connector Body
UPC	781786618602

## Dimensions

Dimensions	2.44 in x 2.44 in x 6.00 in
Display Size	Standard Sized Product
Height	6.00 in
Length	2.44 in
Width	2.44 in

## Electrical Ratings

Amperage Rating	20A/30 A
Connectivity	Pressure Terminal Screws
Current Rating	20A/30 A
Voltage Rating	250 VDC/600 VAC
Voltage Rating Description	250 VDC/600 VAC

## Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire
Wire Size	#18 AWG to #8 AWG

## Logistics

Carton Quantity	5
-----------------	---

## Product Assets

[Catalog Page - Bryant H-25 Catalog page](#)  
[Catalogs - Bryant Full Line Catalog](#)

## Related Products

- 21415 - Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal and White
- 20418 - Locking Devices, Bryant Power Interrupting, Flanged Inlet, 30A 3-Phase Delta 480V AC, Non-NEMA, Screw Terminal, Cast Aluminum, FS/FD Mounted
- 21447 - Locking Devices, Bryant Power Interrupting, Industrial, Flanged Inlet, 30A 250V DC/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Surface Mounted
- 20424 - Locking Devices, Bryant Power Interrupting, Accessories, Weatherproof Boot for Connector, For 30A Black Rubber
- SAB12A - Locking Devices, Twist-Lock®, Accessories, 1/2" NPT Conduit Adapter



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRY-21414-SPEC-EN | REV 5/2023