



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 20A 125V/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal

By Bryant
Catalog # 23000G



Locking Devices, Bryant Power Interrupting, Industrial, Receptacle, 20A 125V AC or DC/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black Phenolic, Back Wired

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Thermoset molded housing provides maximum heat resistance

Application

Industrial Grade

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/20A Flush Single Receptacle
Material	Composite
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Bryant
Style	Grounding
Type	Receptacle
UPC	781786618824

Dimensions

Dimensions	3.28 in x 1.62 in x 1.47 in
Display Size	Standard Sized Product
Height	1.47 in
Length	3.28 in
Width	1.62 in

Electrical Ratings

Amperage Rating	10A/20 A
Connectivity	Pressure Terminal Screws
Current Rating	10A/20 A
Phase	Single Phase
Voltage Rating	125 VAC/125 VDC/250 VDC/480 VAC
Voltage Rating Description	125V AC or DC/250V DC, 480V AC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - Bryant H-24 Catalog page](#)
[Catalogs - Bryant Full Line Catalog](#)

Related Products

- [SB7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.40" Opening, Standard Size, Brass](#)
- [23005G - Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, Non-NEMA](#)
- [23007 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, For 20A Bryant Power Interrupting, Standard Size, Cast Aluminum](#)
- [7418B - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1\) 1.40" Opening, Standard Size, Cast Aluminum](#)
- [SS7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) 1.40" Opening, Standard Size, Stainless Steel](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRY-23000G-SPEC-EN | REV 5/2023