



Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V/10A 250V DC 480V AC, Non-NEMA

By Bryant
Catalog # 23005

Locking Devices, Bryant Power Interrupting, Industrial, Male Plug, 20A 125V AC or DC/10A 250V DC 480V AC, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White



Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

General

Application	Extra Heavy Duty Industrial
Catalog Number	23005
Color	Black, White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/20A Male Nylon Non-Grounding Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Bryant
Style	Non-Grounding
Type	Plugs
UPC	781786618879

Dimensions

Dimensions	1.62 in x 1.62 in x 3.56 in
Display Size	Standard Sized
Height	3.56 in
Length	1.62 in
Width	1.62 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current Rating	20 A
Phase	Multi Phase
Voltage Rating	125 VAC/125 VDC/250 VDC/480 VDC
Voltage Rating Description	125 VAC/125 VDC/250 VDC/480 VDC
Wattage	

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - BRY H-24 Catalog Page](#)
[Catalogs - Bryant Full Line Catalog](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRY-23005-SPEC-EN | REV 6/2024